

SPICE PARAMETER
QS6J3

by ROHM TR Div.

```
* QS6J3 PMOSFET model
* Date: 2006/09/11
* This model includes a diode between drain and source.
*****D G S
.SUBCKT QS6J3 1 2 3
M1 1 2 3 3 MOS_P
D1 1 3 DREV
.MODEL MOS_P PMOS
+ LEVEL=3
+ L=2.0000E-6
+ W=1
+ KP=13.194E-6
+ RS=10.000E-3
+ RD=94.954E-3
+ VTO=-1.5862
+ RDS=1.0000E6
+ TOX=2.0000E-6
+ CGSO=264.00E-12
+ CGDO=55.827E-12
+ CBD=20.685E-12
+ MJ=1.1763
+ RG=40
+ N=2
+ RB=1.0000E-3
+ GAMMA=0
+ KAPPA=0
+ UO=300
.MODEL DREV D
+ IS=393.83E-15
+ N=1.0594
+ RS=.15873
+ IKF=84.994E-3
.ENDS QS6J3
```