Dear customer

LAPIS Semiconductor Co., Ltd. ("LAPIS Semiconductor"), on the 1<sup>st</sup> day of October, 2020, implemented the incorporation-type company split (shinsetsu-bunkatsu) in which LAPIS established a new company, LAPIS Technology Co., Ltd. ("LAPIS Technology") and LAPIS Technology succeeded LAPIS Semiconductor's LSI business.

Therefore, all references to "LAPIS Semiconductor Co., Ltd.", "LAPIS Semiconductor" and/or "LAPIS" in this document shall be replaced with "LAPIS Technology Co., Ltd."

Furthermore, there are no changes to the documents relating to our products other than the company name, the company trademark, logo, etc.

Thank you for your understanding.

LAPIS Technology Co., Ltd.
October 1, 2020





FEDL227XX-06

Issue Date: Oct.16, 2013

# ML2272X-XXX/ML2276X-XXX

Speech Synthesis LSI with Built-in P2ROM Including Speech-Speed Conversion/Pitch Conversion Functions

#### **GENERAL DESCRIPTION**

The ML2272X(ML22725/ML22724/ML22723-XXX) and ML2276X(ML22765/ML22764/ML22763-XXX) are speech synthesis LSIs with built-in P2ROM that stores speech data.

These LSIs include speech speed conversion, pitch conversion, edit ROMs, ADPCM2 decoders, 16-bit DA converters, low pass filters, and monaural speaker amplifiers. The ML2272X supports the synchronous serial interface and the ML2276X supports the I2C interface. By integrating all the functions required for speech output into a single chip, these LSIs can be more easily incorporated in compact portable devices.

• Built-in memory capacity and maximum vocal reproduction time:

the following table (in 4-bit ADPCM2 mode)

| Product name        | DOM consoity | Maximum vocal reproduction time (sec) * |                         |                        |  |  |
|---------------------|--------------|---|-------------------------|------------------------|--|--|
| Product flame       | ROM capacity | $F_S = 8.0 \text{ kHz}$                 | F <sub>S</sub> = 16 kHz | $F_S = 32 \text{ kHz}$ |  |  |
| ML22725-XXX/ML22765 | 16 Mbits     | 522                                     | 261                     | 130                    |  |  |
| ML22724-XXX/ML22764 | 8 Mbits      | 260                                     | 130                     | 64                     |  |  |
| ML22723-XXX/ML22763 | 4 Mbits      | 129                                     | 64                      | 32                     |  |  |

(\*: Speech -speed or pitch conversion functions is not used.)

• voice synthesis method: 4-bit ADPCM2

8-bit Nonlinear PCM 8-bit PCM, 16-bit PCM

Can be specified for each phrase.

• Sampling frequency( $F_s$ ): 4.0 / 5.3 / 6.4 / 8.0 / 10.6 / 12.0 / 12.8 / 16.0 / 21.3 / 24.0 / 25.6 / 32.0 /

48.0 kHz

F<sub>S</sub> can be specified for each phrase.

• Built-in low-pass filter and 16-bit DA converter

• Speaker driving amplifier:  $0.7 \text{ W } (8\Omega \text{ , DV}_{DD}=5 \text{ V, Ta}=25^{\circ}\text{C})$ 

Analog input: 2ch (internal: 1ch, external: 1ch)

• CPU command interface: 3-wired serial clock-synchronized (ML2272X)

I2C interface (ML2276X)

• Maximum number of phrases: 4096 phrases, from 000h to 3FFh (1024 phrases/bank)

• Memory bank switching: Enabled between bank 1 and bank 4 using the SEL0 and SEL1 pins.

• Volume control: 32 levels (OFF is included) can be set by CVOL command.

50 levels (OFF is included) can be set by AVOL command.

• Repeat function: LOOP commands

• Speech speed conversion function ×0.50 to ×2.00 (150 levels: 0.01 step)
• Pitch conversion function ±20% (40 levels: 1% step width)

• Source oscillation frequency: 4.096 MHz

• Power supply voltage: 2.7 to 3.6V / 4.5 to 5.5 V

• Operating temperature range: -40°C to +85°C

• Package: 30-pins plastic SSOP (SSOP30-P-56-0.65-K-MC)

• Product name: ML22725-xxxMB,ML22724-xxxMB, ML22723-xxxMB

ML22765-xxxMB,ML22764-xxxMB, ML22763-xxxMB


(xxx: ROM code No.)



The table below summarizes the differences from the ML2216 and ML22800 series.


| Parameter  | ML2216  | ML22800 series        | ML22725/ML22724/<br>ML22723-XXX  | ML22765/ML22764/<br>ML22763-XXX |
|--|---|-----------------------|--|---------------------------------|
| CPU interface  | Serial  | ←                     | ←  | I2C                             |
| Playback method  | 4-bit ADPCM2 8-bit straight PCM 8-bit nonlinear PCM 16-bit straight PCM | <b>←</b>              | <b>←</b>   | <b>←</b>                        |
| Maximum number of phrases  | 256   | 1024 (256/bank)       | 4096 (1024/bank)   | <b>←</b>                        |
| Sampling frequency<br>(kHz)  | 4.0/5.3/6.4/<br>8.0/10.6/12.8<br>16.0                                   | ↓                     | 4.0/5.3/6.4/8.0/<br>10.6/12.0/12.8/<br>16.0/21.3/24.0/<br>25.6/32.0/48.0 | <b>←</b>                        |
| Clock frequency  | 4.096MHz<br>(with a built-in crystal<br>oscillator circuit)             | <b>+</b>              | <b>←</b>   | <b>←</b>                        |
| D/A converter  | 12 bits   | 12 bits               | 16 bits  | ←                               |
| Low-pass filter  | 3rd order comb filter   | 3rd order comb filter | FIR interpolation filter   | ←                               |
| Speaker driving amplifier  | Built-in 0.3W $(8\Omega, DV_{DD} = 5 V)$                                | No                    | Built-in 0.7W $(8\Omega, DV_{DD} = 5 V)$                                 | <b>←</b>                        |
| Speech speed/pitch conversion  | No  | <b>←</b>              | Yes  | <b>←</b>                        |
| Edit ROM function  | Yes   | <b>+</b>              | <b>←</b>   | ←                               |
| Volume control   | 16 levels   | ←                     | 32 levels  | ←                               |
| Silence insertion  | Yes<br>20 ms to 1024 ms<br>(4 ms/step)                                  | <b>←</b>              | ←  | <b>←</b>                        |
| Repeat function  | Yes   | ←                     | ←  | ←                               |
| Interval at which a seam is silent during continuous playback (Note) | No  | <b>←</b>              | <b>←</b>   | <b>←</b>                        |
| Power supply voltage   | 2.7 V to 5.5 V  | 2.7 V to 3.6 V        | 2.7 V to 5.5 V   | <b>←</b>                        |
| Package  | 44-pin QFP  | 30-pin SSOP           | <b>←</b>   | <b>←</b>                        |

<sup>\*1:</sup> Continuous playback as shown below is possible.






# BLOCK DIAGRAMS (ML22725/ML22724/ML22723-XXX)



## (ML22765/ML22764/ML22763-XXX)





# **PIN CONFIGURATIONS (TOP VIEW)**


# ML22725/ML22724/ML22723-XXXMB (Synchronous serial interface)

|  |            | 1  |  |
|--|------------|--|--|
| AIN 1 TESTI0 2 RESETB 3 TESTO 4 DIPH 5 SEL0 6 SEL1 7 DGND 8 CSB 9 SCK 10 SI 11 SO 12 |            | 30<br>29<br>28<br>27<br>26<br>25<br>24<br>23<br>22<br>21<br>20 | SPM<br>SPP<br>SPGND<br>SPV <sub>DD</sub><br>DGND<br>SG<br>TESTI1<br>V <sub>DDR</sub><br>DV <sub>DD</sub><br>V <sub>DDL</sub><br>NC<br>DGND |
| SI 11  |            |  | NC   |
| CBUSYB 13  |            | 18   | NC   |
| DGND 14<br>XT 15   | $\bigcirc$ | 17<br>16   | DV <sub>DD</sub><br>XTB  |

NC: No Connection

# 30-Pin Plastic SSOP

## ML22765/ML22764/ML22763-XXXMB (I2C interface)



NC: No Connection

30-Pin Plastic SSOP



# PIN DESCRIPTION (COMMON TO ALL PRODUCTS)

| Pin              | Symbol            | I/O | Initial value<br>(*1) | Description   |
|------------------|-------------------|-----|-----------------------|---|
| 1                | AIN               | I   | 0                     | Input pin for speaker amplifier.  |
| 2                | TESTI0            | I   | 0                     | Input pin for testing. Fix this pin to "L" level (DGND level). This pin has a pull-down resistor built in.  |
| 3                | RESETB            | I   | 0<br>(*2)             | Input pin for reset At the "L" level, the LSI enters initial state. During reset, the entire circuitry stops and enters power down state. Input "L" level when power is supplied. After the power supply voltage is stable, drive this pin to "H" level. Then the entire circuitry can be powered up. This pin has a pull-up resistor built in. |
| 4                | TESTO             | 0   | Hi-Z                  | Output pin for testing. Leave this pin open.  |
| 6, 7             | SEL0<br>SEL1      | Ι   | 0                     | Memory bank switching pins. Fix these pins to "L" level when the memory bank function is not used.  |
| 8, 14,<br>19, 26 | DGND              |     | _                     | Digital ground pin. Also serves as a ground pin for the internal memory.  |
| 13               | CBUSYB            | 0   | 1                     | Output pin for command processing status  This pin outputs "L" level during command processing. Any command should be entered when this pin is "H" level.   |
| 15               | ХТ                | ı   | 0                     | Connect to the crystal or ceramic resonator. A feedback resistor around 1 $M\Omega$ is built in between this pin and the XTB pin. Use this pin if need to use an external clock. If the resonator is used, connect it as close to this pin as possible.   |
| 16               | ХТВ               | 0   | 1                     | Connects to the crystal or ceramic resonator.  When to use an external clock, leave this pin open.  If the resonator is used, connect it as close to this pin as possible.  |
| 17, 22           | DV <sub>DD</sub>  | _   | _                     | Power supply pins for logic circuitry. Connect a capacitor of 0.1 $\mu\text{F}$ or more between these pins and DGND pins.   |
| 18, 20           | N.C               | _   | _                     | No-connected pins. Leave these pins open.   |
| 21               | V <sub>DDL</sub>  | _   | 0                     | Regulator output pin for internal logic circuitry.  Connect a capacitor recommended between this pin and DGND pin.  |
| 23               | $V_{DDR}$         | _   | 0                     | Regulator output pin for Built-in ROM.  Connect a capacitor recommended between this pin and DGND pin.  |
| 24               | TESTI1            | -   | 0                     | Input pin for testing. Fix this pin to "L" level (DGND level). This pin has a pull-down resistor built in.  |
| 25               | SG                |     | 0                     | Reference voltage output pin for the speaker amplifier built-in.  Connect a capacitor recommended between this pin and DGND pin.  |
| 27               | SPV <sub>DD</sub> | _   | _                     | Power supply pin for the speaker amplifier.  Connect a bypass capacitor of 0.1 F or more between this pin and SPGND pin.  |
| 28               | SPGND             | _   | _                     | Ground pin for the speaker amplifier.   |
| 29               | SPP               | 0   | 0                     | Positive(+) output pin of the speaker amplifier built-in. Serves as the LINE output (*3), if built-in speaker amplifier is not used.  |
| 30               | SPM               | 0   | Hi-Z                  | Negative(-) output pin of the speaker amplifier built-in.   |



# PIN DESCRIPTION (FOR ML2272X SYNCHRONOUS SERIAL INTERFACE)

| Pin | Symbol | I/O | Initial value<br>(*1) | Description  |
|-----|--------|-----|-----------------------|--|
| 5   | DIPH   | ı   | 0                     | Set pin of the SCK clock edge.  When this pin is "L" level, rising edge is available for input(SI) and falling edge is available for output(SO).  When this pin is "H" level, falling edge is available for input(SI) and rising edge is available for output(SO).                     |
| 9   | CSB    | I   | 1                     | Chip select pin. At the "L" level, data input/output is available.   |
| 10  | SCK    | I   | 0                     | Synchronous clock input pin for serial interface.  |
| 11  | SI     | ı   | 0                     | Input pin of synchronous serial data.  When the DIPH pin is "L" level, data is shifted in at the rising edges of the SCK clock pulses.  When the DIPH pin is "H" level, data is shifted in at the falling edges of the SCK clock pulses.   |
| 12  | so     | 0   | Hi-Z                  | Output pin of synchronous serial data. When the DIPH pin is "L" level, data is output at the falling edges of the SCK clock pulses. When the DIPH pin is "H" level, data is output at the rising edges of the SCK clock pulses. When the CSB pin is "H" level, this pin is Hi-Z state. |

<sup>\*1:</sup> Indicates the initial value during reset input or power down.

<sup>\*1:</sup> Indicates the initial value during reset input or power down.

<sup>\*2: &</sup>quot;H" during power down.

<sup>\*3:</sup> Outputs a voice signal before amplified by the speaker amplifier built-in.



# PIN DESCRIPTION (FOR ML2276X I2C INTERFACE)

| Pin      | Symbol               | I/O | Initial value<br>(*1) | Description   |
|----------|----------------------|-----|-----------------------|---|
| 5, 9, 12 | SAD0<br>SAD1<br>SAD2 | ı   | 0                     | Set pin of the slave address.   |
| 10       | SCL                  | ı   | 0                     | Clock input pin for I2C serial interface. This pin should be connected to pull-up resistor.   |
| 11       | SDA                  | Ю   | 0                     | Input/output pin for I2C serial data. Use for setting the mode of write/read and writing address, writing data or reading data. This pin should be connected to pull-up resistor. (N-ch MOS) open drain, when output mode. High impedance(Hi-Z), when input mode. |

<sup>\*1:</sup> Indicates the initial value during reset or power down.



## ABSOLUTE MAXIMUM RATINGS

 $(DGND = SPGND = 0 V, Ta = 25^{\circ}C)$ 

|                              |                   |  | (50.15                        | 0 t, ia 20 0) |
|------------------------------|-------------------|--|-------------------------------|---------------|
| Parameter                    | Symbol            | Condition  | Rating                        | Unit          |
| Power supply voltage         | $DV_DD, \ SPV_DD$ | _  | -0.3 to +7.0                  | V             |
| Input voltage                | $V_{IN}$          |  | -0.3 to DV <sub>DD</sub> +0.3 | V             |
| Power dissipation            | P <sub>D</sub>    | _  | 938                           | mW            |
| ·                            |                   | Applies to all pins except SPM, SPP, $V_{DDL}$ , and $V_{DDR}$ . | 10                            | mA            |
| Output short-circuit current | I <sub>OS</sub>   | Applies to SPM and SPP pins.                                     | 300                           | mA            |
|                              |                   | Applies to $V_{DDL}$ and $V_{DDR}$ pins.                         | 50                            | mA            |
| Storage temperature          | T <sub>STG</sub>  | _  | −55 to +150                   | °C            |

# RECOMMENDED OPERATING CONDITIONS

(DGND = SPGND = 0 V)

| Parameter                                  | Symbol            | Condition | Range      |       |      | Unit    |
|--|-------------------|-----------|------------|-------|------|---------|
| Power supply voltage                       | $DV_DD, \ SPV_DD$ | _         | 2.7 to 5.5 |       |      | V       |
| Operating temperature                      | T <sub>OP</sub>   | _         | -40 to +85 |       |      | °C      |
| Master clock frequency                     | f <sub>osc</sub>  | _         | Min.       | Тур.  | Max. | MHz     |
|  |                   |           | 3.5        | 4.096 | 4.5  | IVII IZ |
| External capacitors for crystal oscillator | Cd, Cg            | _         | 15         | 30    | 45   | pF      |



# **ELECTRICAL CHARACTERISTICS**

# DC Characteristics (for the 3V applications)

 $DV_{DD} = SPV_{DD} = 2.7 \text{ to } 3.6 \text{ V}, DGND = AGND = 0 \text{ V}, Ta = -40 \text{ to } +85^{\circ}\text{C}$ 

| DVDD = 3FVDD = 2.7  to 3.0 V, DGND = AGND = 0  V, Ta = -40  to |                   |  |                       |      |                       | 0 100 0 |
|--|-------------------|--|-----------------------|------|-----------------------|---------|
| Parameter  | Symbol            | Condition                                      | Min.                  | Тур. | Max.                  | Unit    |
| "H" input voltage  | $V_{IH}$          | _  | $0.86 \times DV_{DD}$ |      | $DV_DD$               | V       |
| "L" input voltage  | $V_{IL}$          | _  | 0                     | _    | $0.14 \times DV_{DD}$ | V       |
| "H" output voltage 1   | $V_{OH1}$         | $I_{OH} = -1 \text{ mA}$                       | DV <sub>DD</sub> -0.4 | _    | _                     | V       |
| "H" output voltage 2 (*1)                                      | $V_{OH2}$         | $I_{OH} = -50 \mu A$                           | DV <sub>DD</sub> -0.4 | _    | _                     | V       |
| "L" output voltage 1   | $V_{OL1}$         | $I_{OL} = 2 \text{ mA}$                        | _                     | _    | 0.4                   | V       |
| "L" output voltage 2 (*1)                                      | $V_{OL2}$         | I <sub>OL</sub> = 50 μA                        | _                     |      | 0.4                   | V       |
| "L" output voltage 3 (*2)                                      | $V_{OL3}$         | $I_{OL} = 3 \text{ mA}$                        | _                     | _    | 0.4                   | V       |
| "H" input current 1  | I <sub>IH1</sub>  | $V_{IH} = DV_{DD}$                             | _                     |      | 10                    | μΑ      |
| "H" input current 2 (*3)                                       | I <sub>IH2</sub>  | $V_{IH} = DV_{DD}$                             | 0.3                   | 2.0  | 15                    | μΑ      |
| "H" input current 3 (*4)                                       | I <sub>IH3</sub>  | $V_{IH} = DV_{DD}$                             | 2                     | 30   | 200                   | μΑ      |
| "L" input current 1  | I <sub>IL1</sub>  | V <sub>IL</sub> = GND                          | -10                   | _    | _                     | μΑ      |
| "L" input current 2 (*3)                                       | I <sub>IL2</sub>  | V <sub>IL</sub> = GND                          | -15                   | -2.0 | -0.3                  | μA      |
| "L" input current 3 (*5)                                       | I <sub>IL3</sub>  | V <sub>IL</sub> = GND                          | -200                  | -30  | -2                    | μΑ      |
| "H" output leak current 3 (*6)                                 | I <sub>ILOH</sub> | $V_{OH} = DV_{DD}$                             | _                     | _    | 10                    | μA      |
| "L" output leak current 3 (*6)                                 | I <sub>ILOL</sub> | V <sub>OL</sub> = GND                          | -10                   | _    | ı                     | μΑ      |
| Supply current during playback                                 | I <sub>DD</sub>   | f <sub>OSC</sub> = 4.096 MHz<br>No output load | _                     | _    | 20                    | mA      |
| Power-down supply  | land              | Ta = -40 to +40°C                              | _                     | 1    | 10                    | μA      |
| current  | I <sub>DDS</sub>  | Ta = -40 to +85°C                              | _                     | 1    | 20                    | μA      |

<sup>\*1:</sup> Applies to the XTB pin.

<sup>\*2:</sup> Applies to the SCL and SDA pins.

<sup>\*3:</sup> Applies to the XT pin.

<sup>\*4:</sup> Applies to the TESTI0 pin.

<sup>\*5:</sup> Applies to the RESETB pin.

<sup>\*6:</sup> Applies to the TESTO pin.



# DC Characteristics (for the 5V applications)

| $DV_{DD} = SPV_{DD} = 4.5 \text{ to}$ | 5.5 V, DGND = SPGND : | = 0 V, Ta = −40 to +85°C |
|---------------------------------------|-----------------------|--------------------------|
|                                       |                       |                          |

| Davamatar                      | Cumphal            | Condition                                      |                       |      | 1                    | ı — — |
|--------------------------------|--------------------|--|-----------------------|------|----------------------|-------|
| Parameter                      | Symbol             | Condition                                      | Min.                  | Тур. | Max.                 | Unit  |
| "H" input voltage              | $V_{IH}$           |  | $0.8 \times DV_{DD}$  | _    | $DV_DD$              | V     |
| "L" input voltage              | $V_{IL}$           | _  | 0                     | _    | $0.2 \times DV_{DD}$ | V     |
| "H" output voltage 1           | $V_{OH1}$          | $I_{OH} = -1 \text{ mA}$                       | DV <sub>DD</sub> -0.4 | _    | _                    | V     |
| "H" output voltage 2 (*1)      | $V_{OH2}$          | I <sub>OH</sub> = -50μA                        | DV <sub>DD</sub> -0.4 | _    | _                    | V     |
| "L" output voltage 1           | $V_{OL1}$          | $I_{OL} = 2 \text{ mA}$                        | _                     |      | 0.4                  | V     |
| "L" output voltage 2 (*1)      | $V_{OL2}$          | $I_{OL}$ = 50 $\mu$ A                          | _                     | _    | 0.4                  | V     |
| "L" output voltage 3 (*2)      | $V_{OL3}$          | $I_{OL} = 3 \text{ mA}$                        | _                     | _    | 0.4                  | V     |
| "H" input current 1            | $I_{\mathrm{IH1}}$ | $V_{IH} = DV_{DD}$                             | _                     | _    | 10                   | μΑ    |
| "H" input current 2 (*3)       | I <sub>IH2</sub>   | $V_{IH} = DV_{DD}$                             | 0.8                   | 5.0  | 20                   | μA    |
| "H" input current 3 (*4)       | I <sub>IH3</sub>   | $V_{IH} = DV_{DD}$                             | 20                    | 100  | 400                  | μΑ    |
| "L" input current 1            | $I_{\rm IL1}$      | V <sub>IL</sub> = GND                          | -10                   | _    | _                    | μΑ    |
| "L" input current 2 (*3)       | I <sub>IL2</sub>   | V <sub>IL</sub> = GND                          | -20                   | -5.0 | -0.8                 | μΑ    |
| "L" input current 3 (*5)       | I <sub>IL3</sub>   | V <sub>IL</sub> = GND                          | -400                  | -100 | -20                  | μA    |
| "L" output leak current 2 (*6) | I <sub>ILOH</sub>  | $V_{OH} = DV_{DD}$                             |                       | l    | 10                   | μA    |
| "L" output leak current 3 (*6) | I <sub>ILOL</sub>  | V <sub>OL</sub> = GND                          | -10                   | I    | _                    | μΑ    |
| Supply current during playback | I <sub>DD</sub>    | f <sub>OSC</sub> = 4.096 MHz<br>No output load | _                     |      | 25                   | mA    |
| Power-down supply              | 1                  | Ta = -40 to +40°C                              | _                     | 1    | 15                   | μA    |
| current                        | I <sub>DDS</sub>   | Ta = -40 to +85°C                              | _                     | 1    | 30                   | μA    |

<sup>\*1:</sup> Applies to the XTB pin.

<sup>\*2:</sup> Applies to the SCL and SDA pins.

<sup>\*3:</sup> Applies to the XT pin.

<sup>\*4:</sup> Applies to the TESTI0 pin.

<sup>\*5:</sup> Applies to the RESETB pin.

<sup>\*6:</sup> Applies to the TESTO pin.

+50

mV



between SPM and SPP

with no signal present

#### Characteristics of Analog Circuitry (for the 3V applications)

 $DV_{DD}$  =  $SPV_{DD}$  = 2.7 to 3.6 V, DGND = SPGND = 0 V, Ta = -40 to +85°C Parameter Symbol Condition Max. Unit Min. Тур. AIN input resistance  $R_{AIN}$ 15 20 25  $\mathsf{k}\Omega$ AIN input voltage range  $V_{AIN}$  $DV_{DD}\!\!\times\!\!2/3$ Vp-p LINE output load  $R_{\mathsf{LA}}$ During 1/2 DV<sub>DD</sub> output 10  $k\Omega$ resistance LINE output voltage ٧ No output load DV<sub>DD</sub>/6  $DV_{DD} \times 5/6$  $V_{AO}$ range SG output voltage  $V_{SG}$  $0.95 \times V_{DDL}/2$  $V_{\text{DDL}}/2$  $1.05 \times V_{DDL}/2$ V SG output resistance During power down  $R_{SG}$ 57 96 135  $k\Omega$ SPM, SPP output load  $R_{\mathsf{LSP}}$ 8 Ω resistance Speaker amplifier output  $SPV_{DD} = 3.3V, f = 1kHz$  $P_{SPO}$ 100 300 mW  $R_{SPO}$  = 8 $\Omega$ , THD $\geq$ 10% power Output offset voltage SPIN-SPM gain = 0dB

With a load of  $8\Omega$ 

-50

#### **Characteristics of Analog Circuitry (for the 5V applications)**

 $V_{\text{OF}}$ 

 $DV_{DD}$  =  $SPV_{DD}$  = 4.5 to 5.5 V, DGND = SPGND = 0 V, Ta = -40 to +85°C Symbol Parameter Condition Min. Max. Unit Тур. AIN input resistance  $R_{AIN}$ 15 20 25  $k\Omega$ AIN input voltage range  $V_{\text{AIN}}$  $DV_{\text{DD}}\!\!\times\!\!2/3$ Vp-p LINE output load During 1/2 DV<sub>DD</sub> output 10  $k\Omega$  $R_{\text{LA}}$ resistance LINE output voltage ٧  $DV_{DD} \times 5/6$  $V_{AO}$ No output load  $DV_{DD}/6$ range  $V_{SG}$  $0.95 \times V_{DDL}/2$ ٧ SG output voltage  $V_{DDL}/2$  $1.05 \times V_{DDL}/2$ SG output resistance During power down 96 135  $R_{SG}$ 57  $\mathsf{k}\Omega$ SPM, SPP output load 8  $R_{LSP}$ Ω resistance  $SPV_{DD} = 5.0V, f = 1kHz$ Speaker amplifier output  $R_{SPO} = 8\Omega$ , THD $\geq$ 10% 500 700  $\mathsf{mW}$  $P_{SPO}$ power Ta=25°C Output offset voltage SPIN-SPM gain = 0dB between SPM and SPP  $V_{\text{OF}}$ -50+50 mV With a load of  $8\Omega$ with no signal present



#### **AC Characteristics (Common to All Products)**

 $DV_{DD}$  =  $SPV_{DD}$  = 2.7 to 5.5 V, DGND = SPGND = 0 V, Ta = -40 to +85°C Applicable Parameter Symbol Condition Min. Typ. Max. Unit command Master clock duty cycle 40 50 60 %  $f_{duty}$ RESETB input pulse width 100  $t_{RST}$ μS Reset noise rejection pulse width 0.1  $t_{\mathsf{NRST}}$ μS STOP, SLOOP, CLOOP, CVOL,  $t_{\mathsf{INT}}$ 2 μS **AVOL** Command input interval time  $f_{OSC}$  = 4.096 MHz PUP 10 **t**<sub>INTP</sub> ms **RDSTAT** 500 μS **t**INTRD (After status read) SLOOP Command input enable time (Continuous play  $f_{OSC} = 4.096 \text{ MHz}$ 10 ms  $t_{cm}$ by PLAY/MUON)  $f_{OSC} = 4.096 \text{ MHz}$ PUP 2.0 2.5 3.0 t<sub>PUP1</sub> ms **PDWN**  $t_{PD1}$  $f_{OSC} = 4.096 \text{ MHz}$ 20 μS 2nd byte of AMODE  $f_{OSC}$  = 4.096 MHz (PUP = "0" When an external 58 60 62 t<sub>PUPA1</sub> ms DAEN (or SPEN) clock is input **=** "0"→"1") 2nd byte of AMODE (PUP = "1"  $f_{OSC}$  = 4.096 MHz 90 93 95 ms t<sub>PUPA2</sub> CBUSYB "L" level output time DAEN = "0"→"1" SPEN = "0") 2nd byte of AMODE (PUP = "0") $f_{OSC}$  = 4.096 MHz 108 110 112 ms t<sub>PDA1</sub> DAEN (or SPEN) = "1"→<u>"0")</u> 2nd byte of AMODE (PUP = "1" 140 t<sub>PDA2</sub>  $f_{OSC} = 4.096 \text{ MHz}$ 142 144 ms DAEN = "1" →"0" SPEN = "0")

Note: Output pin load capacitance = 45 pF

CBUSYB "L" level output time 1(\*1)

 $t_{CB1}$ 

 $f_{OSC}$  = 4.096 MHz

2

ms

<sup>\*1:</sup> Applies to the case that a command is input except after a PUP, PDWN, or 2nd byte of AMODE command input.



# AC Characteristics of Synchronous Serial Command Interface (Applied to ML2272X)

 $DV_{DD} = SPV_{DD} = 2.7 \text{ to } 5.5 \text{ V}, DGND = SPGND = 0 \text{ V}, Ta = -40 \text{ to } +85^{\circ}\text{C}$ 

|   | D 4 DD - OI        | V DD - 2.7 to      | 75.5 V, DGND - 31 C | <u> </u> | v, ra- | 70 10 | 100 0 |
|---|--------------------|--------------------|---------------------|----------|--------|-------|-------|
| Parameter                                   | Applicable command | Symbol             | Condition           | Min.     | Тур.   | Max.  | Unit  |
| SCK input enable time from CS               | SB fall edge       | t <sub>ESCK</sub>  | _                   | 100      |        |       | ns    |
| SCK hold time from CSB rise e               | edge               | t <sub>CSH</sub>   | _                   | 100      |        |       | ns    |
| Data floating time from CSB ris             | se edge            | t <sub>DOZ</sub>   | $R_L = 3 k\Omega$   | _        | _      | 100   | ns    |
| Data setup time from SCK rise               | edge               | t <sub>DIS1</sub>  | DIPH = "0"          | 50       |        |       | ns    |
| Data hold time from SCK rise e              | edge               | t <sub>DIH1</sub>  | DIPH = "0"          | 50       |        |       | ns    |
| Data output delay time from SCK fall edge   |                    | t <sub>DOD1</sub>  | $R_L = 3 k\Omega$   | _        | _      | 80    | ns    |
| Data setup time from SCK fall               | edge               | t <sub>DIS2</sub>  | DIPH = "1"          | 50       |        |       | ns    |
| Data hold time from SCK fall e              | dge                | t <sub>DIH2</sub>  | DIPH = "1"          | 50       |        |       | ns    |
| Data output delay time from SC              | CK rise edge       | t <sub>DOD2</sub>  | $R_L = 3 k\Omega$   | _        |        | 80    | ns    |
| SCK "H" level pulse width                   |                    | t <sub>SCKH</sub>  | _                   | 100      |        |       | ns    |
| SCK "L" level pulse width                   |                    | t <sub>SCKL</sub>  | _                   | 100      |        |       | ns    |
| CBUSYB output delay time from SCK rise edge |                    | t <sub>DBSY1</sub> | DIPH = "0"          | _        |        | 150   | ns    |
| CBUSYB output delay time from               | m SCK fall edge    | t <sub>DBSY2</sub> | DIPH = "1"          | _        | _      | 150   | ns    |

Note: Output pin load capacitance = 45 pF

## AC Characteristics of I2C Command Interface (Applied to ML2276X)

 $DV_{DD}$  =  $SPV_{DD}$  = 2.7 to 5.5 V, DGND = SPGND = 0 V, Ta = -40 to +85°C


| Parameter   | ĺ                   |         | ed mode) |      |
|---|---------------------|---------|----------|------|
| Parameter   | Symbol              | Min.    | Max.     | Unit |
| SCL clock frequence   | t <sub>SCL</sub>    | 0       | 400      | kHz  |
| Hold time for (repeated) START condition                        | T                   | 0.6     |          | 6    |
| After this period, the first clock pulse is generated.          | $T_{HD;STA}$        | 0.0     | _        | μS   |
| SCL "L" level pulse width                                       | $t_{LOW}$           | 1.3     | _        | μS   |
| SCL "H" level pulse width                                       | t <sub>HIGH</sub>   | 0.6     | _        | μS   |
| Setup time for repeated START condition                         | t <sub>SU;STA</sub> | 0.6     | _        | μS   |
| Data hold time: For I2C bus devices                             | t <sub>HD;DAT</sub> | 0       | 0.9      | μS   |
| Data setup time   | t <sub>SU;DAT</sub> | 100     | _        | ns   |
| SDA and SCL signal rise time                                    | t <sub>r</sub>      | 20      | 300      | ns   |
| SDA and SCL signal fall time                                    | t <sub>f</sub>      | 20      | 300      | ns   |
| Setup time for STOP condition                                   | t <sub>su;sto</sub> | 0.6     | _        | μS   |
| Bus free time between STOP condition and START condition        | t <sub>BUF</sub>    | 1.3     | _        | μS   |
| Capacitive load for each bus line                               | C <sub>b</sub>      | _       | 400      | PF   |
| Noise margin at a "L" level in each device connected (including | W                   | 0.1×    |          | V    |
| hysteresis)   | $V_{nL}$            | $DV_DD$ | _        | V    |
| Noise margin at a "H" level in each device connected (including | $V_{nH}$            | 0.1×    |          | V    |
| hysteresis)   | <b>∨</b> nH         | $DV_DD$ | _        | V    |

Note: Output pin load capacitance = 45 pF




## **TIMING DIAGRAMS**

# **Power-On Timing**




Oscillation is stopped after power-on.

# **Power-Up Timing**






# Power-Down Timing (At the PDWN command Input)




# **Power-Down Timing (At the RESETB Input)**



Note: The same timing is applied in the case that the RESETB signal is input during command waiting.




# Playback Start Timing by the PLAY Command




Note: The time length of "L" level of BUSYB is  $t_{\text{CB1}}$  + voice reproduction time.

# **Playback Stop Timing**






#### Continuous Playback Timing by the PLAY Command



\*1: The time length of "L" level of the NCR signal during playback varies depending on the input timing of command.


## Silence Insertion Timing by the MUON Command




\*1: The time length of "L" level of the NCR signal during playback or silence insertion varies depending on the input timing of command.



## Repeat Playback Set/Release Timing by the SLOOP and CLOOP Commands




## Timing of Volume Change by the CVOL Command







# Serial Command Interface Timing (Applied to ML2272X) when DIPH pin is "L" level ( Rise edge for input, fall edge for output)



# Serial Command Interface Timing (Applied to ML2272X) when DIPH pin is "H" level ( Fall edge for input, rise edge for output)



## I2C Command Interface Timing (Applied to ML2276X)





#### **FUNCTIONAL DESCRIPTION**

#### Synchronous Serial Command Interface (Applied to ML2272X)

The CSB, SCK, SI, and SO pins are used to input the command data or to read the status. Driving the CSB pin to "L" level enables the serial CPU interface.

After the CSB pin is driven to "L" level, the command data are input through the SI pin from the MSB synchronized with the SCK clock. The command data shifts in through the SI pin at the rising or falling edge of the SCK clock pulse. Then, a command is executed at the rising or falling edge of the eighth pulse of the SCK clock.

As for status reading, status is output from the SO pin, synchronized with the SCK clock after the CSB pin is driven to "L" level.

The SCK clock edge is specified by the input level of the DIPH pin.


- When the DIPH pin is "L" level, rising edge is available for input from SI pin and falling edge is available for output from SO pin.
- When the DIPH pin is "H" level, falling edge is available for input from SI pin and rising edge is available for output from SO pin.

It is possible to input command data, even if the CSB pin is fixed by "L" level. However, if unexpected pulses caused by noise are induced through the SCK pin, SCK clock pulses are incorrectly counted, causing a failure in normal recognition of command. Then it is recommended that the CSB pin is "L" level only for command input.


The count of the SCK clock pulse is initialized when the CSB pin goes to "H" level.

#### Command Data Input or Status Read Timing

• When DIPH pin is "L" level



• When DIPH pin is "H" level





The following table shows the contents of each data output at a status read.

|     | Output status signal |
|-----|----------------------|
| MSB | _                    |
| 7SB | _                    |
| 6SB | _                    |
| 5SB | BUSYB output         |
| 4SB | _                    |
| 3SB | _                    |
| 2SB | _                    |
| LSB | NCR output           |

The BUSYB output is "L" level when a command is being processed or playback is going on. In other states, the BUSYB output is "H" level. The NCR signal output is "L" level when a command is being processed or playback is in a standby state. In other states, the NCR output is "H" level.



#### I2C Command Interface (Applied to ML2276X)

The I2C Interface built-in is an serial interface (: slave side) that is compliant with I2C bus specification. It supports Fast mode and enables data transmission/reception at 400 kbps. The SCL and SDA pins are used to input the command data or to read the status. Pins (:SAD0, 1 and 2) are used to set the slave address. Pull-up resister should be connected to SCL pin and SDA pin.

For the master on the I2C bus to communicate with this device (: slave), input the slave address with the first seven bits after setting the start condition. The upper three bits of the slave address can be set using the SAD0 to 2 pins. The eighth bit of slave address is used to set the direction (: write or read) of communication. If the eighth bit is "0" level, it is write mode from master to slave. And, if the eighth bit is "1" level, it is read mode from master.


The communication is made in the unit of byte. And acknowledge is needed for each byte.

The protocol of I2C communication is shown below.

24 Command flow at data write

Start condition
Slave address +W(0)
Write address (ex. 1<sup>st</sup> byte of a command)
Write data (ex. 2<sup>nd</sup> byte of a command)
STOP condition


#### • Data write timing



24 Command flow at the data read

Start condition Slave address +R (1) Read data (ex. Status read) STOP condition

#### Data read timing





Setting of the slave address using the SAD0 to 2 pins

| SAD2 | SAD1 | SAD0 | Lower 4 bits |
|------|------|------|--------------|
| 0    | 0    | 0    | 0101         |
| 0    | 0    | 1    | 0101         |
| 0    | 1    | 0    | 0101         |
| 0    | 1    | 1    | 0101         |
| 1    | 0    | 0    | 0101         |
| 1    | 0    | 1    | 0101         |
| 1    | 1    | 0    | 0101         |
| 1    | 1    | 1    | 0101         |

The following table shows the contents of each data output at the status read. Status is updated by the RDSTAT command, therefore, be sure to input the RDSTAT command in order to read status.

|     | Output status signal  |
|-----|-----------------------|
| MSB |                       |
| 7SB |                       |
| 6SB |                       |
| 5SB | BUSYB output (BUSYB0) |
| 4SB |                       |
| 3SB |                       |
| 2SB |                       |
| LSB | NCR output (NCR0)     |

The BUSYB signal is "L" level when either a command is being processed or the playback of a particular channel is going on. In other states, the BUSYB signal is "H" level. The NCR signal is "L" level when either a command is being processed or a particular channel is in standby for playback. In other states, the NCR signal is "H" level.



## **Command List**

Each command is configured in 1-byte (8-bit) units. Each of the AMODE, AVOL FADR, PLAY, MUON, CVOL, VPITCH, and VSPD commands forms one command by two bytes.

| Command | D7  | D6   | D5   | D4   | D3   | D2   | D1   | D0  | Description  |
|---------|-----|------|------|------|------|------|------|-----|--|
| PUP     | 0   | 0    | 0    | 0    | 0    | 0    | S1   | S0  | Power-up command. Shift from the power down state to the command waiting state. Also, sets the number of memory banks.   |
| PDWN    | 0   | 0    | 1    | 0    | 0    | 0    | 0    | 0   | Power-down command. Shift from the command waiting state to the power down state.  |
| RDSTAT  | 1   | 0    | 1    | 1    | 0    | 0    | 0    | 0   | Status read command. Read the command status.  |
|         | 0   | 0    | 0    | 0    | 0    | 1    | 0    | 0   | Control command of analog circuitry.   |
| AMODE   | FAD | DAG1 | DAG0 | AIG1 | AIG0 | DAEN | SPEN | POP | Set operation of power-up/dpwn and input/output.   |
| DI AV   | 0   | 1    | 0    | 0    | F9   | F8   | 0    | 0   | Playback start command.  |
| PLAY    | F7  | F6   | F5   | F4   | F3   | F2   | F1   | F0  | Use the data of the 2 <sup>nd</sup> byte to specify a phrase number.   |
| STOP    | 0   | 1    | 1    | 0    | 0    | 0    | 0    | 0   | Playback stop command.   |
| FADR    | 0   | 0    | 1    | 1    | F9   | F8   | 0    | 0   | Set command of playback phrase.  |
| FADR    | F7  | F6   | F5   | F4   | F3   | F2   | F1   | F0  | Use START command to start.  |
| START   | 0   | 1    | 0    | 1    | 0    | 0    | 0    | 0   | Playback start command without phrase spec. Use FADR command to set phrase. After played back by PLAY command, the same phrase can be played back with this command. |
|         | 0   | 1    | 1    | 1    | 0    | 0    | 0    | 0   | Silence insertion command.   |
| MUON    | M7  | M6   | M5   | M4   | М3   | M2   | M1   | M0  | Set the silent time length using M7 to M0 bits in the 2 <sup>nd</sup> byte.  |
| SLOOP   | 1   | 0    | 0    | 0    | 0    | 0    | 0    | 0   | Set command of repeat playback. Setting is enabled during playback.  |
| CLOOP   | 1   | 0    | 0    | 1    | 0    | 0    | 0    | 0   | Stop command of repeat playback. Also, repeat playback is released by STOP command automatically.  |
|         | 1   | 0    | 1    | 0    | 0    | 0    | 0    | 0   | Volume control command.  |
| CVOL    | 0   | 0    | 0    | CV4  | CV3  | CV2  | CV1  | CV0 | Set volume using CV4 to CV0 bits in the 2 <sup>nd</sup> byte.  |
| AVOL    | 0   | 0    | 0    | 0    | 1    | 0    | 0    | 0   | Analog volume control command.   |
| , WOL   | 0   | 0    | AV5  | AV4  | AV3  | AV2  | AV1  | AV0 | Set volume using AV5 to AV0 bits.  |
| VPITCH  | 1   | 1    | 1    | 0    | 0    | 0    | 0    | 0   | Pitch conversion command.  |
|         | PI7 | PI6  | PI5  | PI4  | PI3  | PI2  | PI1  | PI0 | Can be specified pitch.  |
| VCDD    | 1   | 1    | 0    | 1    | 0    | 0    | 0    | 0   | Speech speed conversion  |
| VSPD    | SD7 | SD6  | SD5  | SD4  | SD3  | SD2  | SD1  | SD0 | command. Can be specified speed.   |



## **Voice Synthesis Algorithm**

Four types of voice synthesis algorithm are supported. They are 4-bit ADPCM2, 8-bit non-linear PCM, 8-bit straight PCM and 16-bit straight PCM. Select the best one according to the characteristics of playback voice.

The following table shows key features of each algorithm.

| Voice synthesis algorithm | Applied waveform                          | Feature  |  |  |
|---------------------------|---|--|--|--|
| 4-bit ADPCM2              | Normal voice waveform                     | Up version of LAPIS Semiconductor's specific voice synthesis algorithm (:4-bit ADPCM).  Voice quality is improved. |  |  |
| 8-bit Nonlinear PCM       | Waveform including high frequency signals | Algorithm which plays back mid-range of waveform as 10-bit equivalent voice quality.                               |  |  |
| 8-bit straight PCM        | (sound effect, etc.)                      | Normal 8-bit PCM algorithm.  |  |  |
| 16-bit straight PCM       | (Souria effect, etc.)                     | Normal 16-bit PCM algorithm,   |  |  |



#### **Memory Allocation and Creating Voice Data**

The ROM is partitioned into four data areas: voice (i.e., phrase) control area, test area, voice area, and edit ROM

The voice control area manages the voice data in the ROM. It contains data for controlling the start/stop addresses of voice data for 1,024 phrases, use/non-use of the edit ROM function and so on.

The test area contains data for testing.

The voice area contains actual waveform data.

The edit ROM area contains data for effective use of voice data. For the details, refer to the section of "Edit ROM Function."

The edit ROM area is not available if the edit ROM is not used.

The ROM data is created using a dedicated tool.

#### Configuration of ROM data

| 0x00000       | Voice control area                                   |
|---------------|--|
| 0x01FFF       | (Fixed 64 Kbits)                                     |
| 0x02000       | Test area  |
| 0x0205F       | rost area  |
| 0x02060       | Voice area   |
| max: 0x1FFFFF |  |
| max: 0x1FFFFF | Edit ROM area<br>Depends on creation<br>of ROM data. |

#### **Playback Time and Memory Capacity**

The playback time depends on the memory capacity, sampling frequency, and playback method.

The equation to know the playback time is shown below. But this is not applied if the edit ROM function is used.

Playback time [sec] = 
$$\frac{1.024 \times (Memory capacity - 64.75 [Kbits])}{Sampling frequency [kHz] \times Bit length}$$

(Bit length is 4 at the 4-bit ADPCM2 and 8/16 at the PCM.)

Example) In the case that the sampling frequency is 16 kHz, algorithm is 4-bit ADPCM2 and ROM capacity is 16 Mbits, the playback time is approx. 261 seconds, as shown below.

Playback time = 
$$\frac{1.024 \times (16834 - 64.75) \text{ [Kbits]}}{16 \text{ [kHz]} \times 4 \text{ [bits]}} \approx 261 \text{ [sec]}$$



#### **Edit ROM Function**

The edit ROM function makes it possible to play back multiple phrases in succession. The following functions are set using the edit ROM function:


• Continuous playback: There is no limit to set the number of times of continuous playback. It

depends on the memory capacity only.


• Silence insertion: 20ms to 1,024 ms

It is possible to use voice ROM effectively to use the edit ROM function. Below is an example of the ROM structure, case of using the edit ROM function.

Example 1) Phrases using the Edit ROM Function



Example 2) Structure of the ROM that contents of example 1 are stored





#### **Memory Bank Switching Function**

The memory bank switching function enables the built-in ROM area that is divivided into up to four banks to be used. When four banks are used, the maximum number of phrases per bank is 1024 so that up to 4096 phrases can be played back.

Using this function, multiple ROM codes can be grouped into one code.

The settings of SEL1 pin and SEL0 pin determines which memory bank is used. To playback phrases, the number of memory banks must be specified in PUP.

When using a memory bank switching function, data must be divided and saved in the specified areas at ROM data creation.

- When the number of memory banks is 1

| SEL1 | SEL0 | ML22725-XXX<br>ML22765-XXX | ML22724-XXX<br>ML22764-XXX | ML22723-XXX<br>ML22763-XXX |  |  |
|------|------|----------------------------|----------------------------|----------------------------|--|--|
| 0    | 0    | 00000h – 1FFFFFh           | 00000h – FFFFFh            | 00000h -7FFFFh             |  |  |

- When the number of memory banks is 2

| SEL1 | SEL0 | ML22725-XXX<br>ML22765-XXX | ML22724-XXX<br>ML22764-XXX | ML22723-XXX<br>ML22763-XXX |
|------|------|----------------------------|----------------------------|----------------------------|
| 0    | 0    | 00000h – FFFFFh            | 00000h – 7FFFFh            | 00000h – 3FFFFh            |
| 0    | 1    | 100000h – 1FFFFFh          | 80000h – FFFFFh            | 40000h – 7FFFFh            |

- When the number of memory banks is 4

|      | When the number of memory bunks is |                   |                            |                            |  |  |  |  |
|------|------------------------------------|-------------------|----------------------------|----------------------------|--|--|--|--|
| SEL1 | SEL0 ML22725-XXX<br>ML22765-XXX    |                   | ML22724-XXX<br>ML22764-XXX | ML22723-XXX<br>ML22763-XXX |  |  |  |  |
| 0    | 0                                  | 00000h – 7FFFFh   | 00000h – 3FFFFh            | 00000h – 1FFFFh            |  |  |  |  |
| 0    | 1                                  | 80000h – FFFFFh   | 40000h – 7FFFFh            | 20000h – 3FFFFh            |  |  |  |  |
| 1    | 0                                  | 100000h – 17FFFFh | 80000h – BFFFFh            | 40000h – 5FFFFh            |  |  |  |  |
| 1    | 1                                  | 180000h – 1FFFFFh | C0000h – FFFFFh            | 60000h – 7FFFFh            |  |  |  |  |

The memory (16 Mbits) in the ML22725 is divided as shown below.

| 0-7FFFFh       | Bank 1<br>Capacity: 16 Mbits<br>Max. Phrase count: 1024 | Bank 1<br>Capacity: 8 Mbits<br>Max. Phrase count: 1024 | Bank 1<br>Capacity: 4 Mbits<br>Max. Phrase count: 1024 |
|----------------|---|--|--|
| 80000-FFFFFh   |   |  | Bank 2<br>Capacity: 4 Mbits<br>Max. Phrase count: 1024 |
| 100000-17FFFFh | <del></del> -   | Bank 2<br>Capacity: 8 Mbits<br>Max. Phrase count: 1024 | Bank 3<br>Capacity: 4 Mbits<br>Max. Phrase count: 1024 |
| 180000-1FFFFh  |   |  | Bank 4<br>Capacity: 4 Mbits<br>Max. Phrase count: 1024 |
|                | Memory divide count: 1                                  | Memory divide count: 2                                 | Memory divide count: 4                                 |

Memory divide count: 16 Mbits × 1 area

Memory divide count: 2 8 Mbits × 2 areas Memory divide count: 4 4 Mbits × 4 areas



#### **Description of Command Functions**

#### 24 PUP command

| • command                   | Λ | Λ | Λ | Λ | Λ | Λ | <b>Q1</b> | 90 |
|-----------------------------|---|---|---|---|---|---|-----------|----|
| <ul> <li>command</li> </ul> | J | ٥ | 0 | ٥ | 0 | ٥ | 5         | 5  |

The PUP command is used to shift from the power down state to the command waiting state.

This command is only available at the power down state.


Conditions are as follows to enter the power down state.

- 1) When the power is turned on.
- 2) When the RESETB input is "L" level (: rest input).
- 3) When the CBUSYB pin goes to "H" level after inputting the power down command(:PDWN).

The relationship between S1/S0 and the memory banks is as follows:

| S1 | S0 |   |
|----|----|---|
| 0  | 0  | Overall memory area is used.  |
| 0  | 1  | The internal memory is divided into 2 areas. The 2 memory areas are switched with the SEL0 pin.           |
| 1  | 0  | The internal memory is divided into 4 areas. The 4 memory areas are switched with the SEL1 and SEL0 pins. |
| 1  | 1  | Prohibited (The operation is the same as above.)  |

The built-in amplifier is not powered up by this command. It is powered up by the AMODE command.



The regulator output starts operating after the PUP command is entered. Any command will be ignored if entered while oscillation is stabilized. However, if a "L" level is input to the RESETB pin, the LSI enters a power down state immediately.

The built-in amplifier is not powered up by the PUP command. It is powered up by the AMODE command.



#### 2. PDWN command


| <ul> <li>command</li> </ul> | 0 | 0 | 1 | 0 | 0 | 0 | 0 | 0 |
|-----------------------------|---|---|---|---|---|---|---|---|

The PDWN command is used to shift from the command waiting state (: both NCR and BUSYB are "H" level) to the power down state.

Any setting is initialized by this command, so it is necessary to set again after power up.

This command is not available during playback.

To resume playback after entering power down state, input the AMODE and PLAY commands after input the PUP command.



The speaker amplifier stops operation after a lapse of command processing time after the PDWN command is input. At this time, the SPM output of the speaker amplifier goes to "Hi-Z" state to prevent troubles by pop noise .

The status of each output pin is as follows after this command is input or reset pin (:RESETB) is "L" level.

| Analog output pin | State |
|-------------------|-------|
| $V_{DDL}$         | GND   |
| $V_{DDR}$         | GND   |
| SG                | GND   |
| SPM               | HiZ   |
| SPP               | GND   |



## 3. RDSTAT command

| <ul> <li>command</li> </ul> | 1 | 0 | 1 | 1 | 0 | 0 | 0 | 0 |
|-----------------------------|---|---|---|---|---|---|---|---|

The RDSTAT command is used to read the NCR and BUSYB signals that indicate the status of internal operation.


The NCR signal is "L" level while commands are processed, and goes to "H" level at the command waiting state.

The BUSYB signal is "L" level during playback voices.

The command interval time ( :  $t_{\text{INTRD}}$ ) is needed to input the next command after reading status using this command.

The following table shows the contents of each bit of data output.

|     | Output status signal |
|-----|----------------------|
| MSB | _                    |
| 7SB | _                    |
| 6SB | _                    |
| 5SB | BUSYB output         |
| 4SB | _                    |
| 3SB | _                    |
| 2SB | _                    |
| LSB | NCR output           |





#### 4. AMODE command

· command

| 0   | 0    | 0    | 0    | 0    | 1    | 0    | 0   | 1 <sup>st</sup> byte |
|-----|------|------|------|------|------|------|-----|----------------------|
| FAD | DAG1 | DAG0 | AIG1 | AIG0 | DAEN | SPEN | POP | 2 <sup>nd</sup> byte |

The AMODE command uses 2 bytes. This command is used to perform various settings for analog circuitry. This command is not available during power-down state, transition to power-up state, transition to power down state or playback state.

In the case of performing power down using PDWN command during power up of analog circuitry, the setting of power up by AMODE command is retained. Use the AMODE command to perform power down, if need to use different conditions from power up of analog circuitry.

In the case of power up of analog circuitry, input the AMODE command after setting the CVOL command to "00h" (: initial value).

The setting of each bit is shown below.

The setting is initialized by reset release or power up.

The FAD bit specifies whether to perform fade-out processing when the STOP command is input. If this bit is set to "1", fade-out processing is performed during a period of approx. 3 ms after the STOP command is input. The BUSYB signal goes to "H" level after fade-out processing.

| FAD | Fade-out processing           |
|-----|-------------------------------|
| 0   | Not available (initial value) |
| 1   | Available                     |

The DAG1, 0 bits are used to set the gain of the internal DAC signal. The AIG1, 0 bits are used to set the gain of an analog input signal from the AIN pin. They are available only when using the speaker amplifier.

| DAG1 | DAG0 | Volume                          |
|------|------|---------------------------------|
| 0    | 0    | Input OFF                       |
| 0    | 1    | Input ON (-6 dB)                |
| 1    | 0    | Input ON (0 dB) (initial value) |
| 1    | 1    | Prohibited (input ON (0 dB))    |

| AIG1 | AIG0 | Volume                       |
|------|------|------------------------------|
| 0    | 0    | Input OFF (initial value)    |
| 0    | 1    | Input ON (–6 dB)             |
| 1    | 0    | Input ON (0 dB)              |
| 1    | 1    | Prohibited (input ON (0 dB)) |

The DAEN bit controls power-up and power-down of the DAC circuitry.

| DAEN | Status of the DAC circuitry      |
|------|----------------------------------|
| 0    | Power-down state (initial value) |
| 1    | Power-up state                   |



The SPEN bit controls power-up and power-down of the speaker circuitry. When the SPEN bit is "0", SPP pin is the LINE output.

| SPEN | Status of the speaker circuitry  |
|------|----------------------------------|
| 0    | Power-down state (initial value) |
| 1    | Power-up state                   |


The POP bit sets whether to suppress the "pop" noise of the LINE output.

- In the case of setting the POP bit to "0"
  If the DAEN bit is "1", LINE output rises from the GND level to the SG level during a period of the specified time (:t<sub>PUPA1</sub>). If the DAEN bit is "0", LINE output falls from the SG level to the GND level during a period of the specified time (:t<sub>PDA1</sub>).
- In the case of setting the PUP bit to "1" If the DAEN bit is "1", LINE output rises from the GND level to the SG level during a period of the specified time (:t<sub>PUPA2</sub>). If the DAEN bit is "0", LINE output falls from the SG level to the GND level during a period of the specified time (:t<sub>PDA2</sub>).


| POP | Pop noise suppression         |
|-----|-------------------------------|
| 0   | Not available (initial value) |
| 1   | Available                     |



• When POP bit is "0" and DAEN or SPEN bit goes to "1"




• When POP bit is "1", SPEN bit is "0" and DAEN bit goes to "1"






• When POP bit is "0" and DAEN or SPEN bit goes to "0"



• When POP bit = "1", DAEN and SPEN bits = "1"  $\rightarrow$  "0" (Applies only when SPEN = "0")






## 5. PLAY command

| <ul> <li>command</li> </ul> | 0  | 1  | 0  | 0  | F9 | F8 | 0  | 0  | 1 <sup>st</sup> byte |
|-----------------------------|----|----|----|----|----|----|----|----|----------------------|
|                             | F7 | F6 | F5 | F4 | F3 | F2 | F1 | F0 | 2 <sup>nd</sup> byte |

The PLAY command uses 2 bytes. This command is used to start playback phrase. This command is able to input when the NCR signal is "H" level.

For the phrase to be played back, set the phrase address of voice data in the ROM using the F9 to F0 bits.

The following figure shows the timing of playback phrase (F9 to F0 is 01h).



When the 1<sup>st</sup> byte of the PLAY command is input, the device enters a state awaiting input of the 2<sup>nd</sup> byte of the PLAY command after a lapse of command processing time. When the 2<sup>nd</sup> byte of PLAY command is input, the device starts reading the external ROM to get the address information of the phrase to be played back after a lapse of command processing time. Thereafter, playback starts and the playback is performed up to the specified ROM address, then the playback stops automatically.


The NCR signal is "L" level during address control, and goes to "H" level when the address control is completed. Then it is possible to input the PLAY command for the next playback phrase.

The BUSYB signal is "L" level during address control and playback, and goes to "H" level when playback is completed. Then it is possible to know whether the playback is going on by the BUSYB signal.



## The PLAY Command Input Timing for Continuous Playback

In the case of continuous playback, input the PLAY command for the next phrase within the command input enable time (:  $t_{cm}$ ) after NCR goes to "H" level. Then it is possible to start playback the next phrase without any silent interval between phrases.



As shown in the diagram above, if continuous playback is carried out, input the PLAY command for the second phrase within 10 ms (tcm) after NCR goes "H". This will make it possible to start playing the second phrase immediately after the playback of the first phrase finishes. Phrases can thus be played continuously without inserting silence between phrases.



## 6. STOP command


| <ul> <li>command</li> </ul> | 0 | 1 | 1 | 0 | 0 | 0 | 0 | 0 |
|-----------------------------|---|---|---|---|---|---|---|---|

The STOP command is used to stop playback.

If the playback is stopped, the NCR and BUSYB signals go to "H" level.

Although it is possible to input this command regardless of the status of NCR during playback, a prescribed command interval time  $(:t_{INT})$  is needed.

The STOP command is not available during power down, transition to power-up or transition to power-down. The playback related command (:PLAY, START or MUON) is not available during STOP command processing.



The playback related command (:PLAY, START or MUON), used on after the STOP command, should be input after confirming the completion (: NCR is "H" and BUSYB is "H") of this command processing by the RDSTAT command, or waiting for 12ms from transition of the CBUSYB to "H" level.



## 7. FADR command

· command

| 0  | 0  | 1  | 1  | F9 | F8 | 0  | 0  | 1 <sup>st</sup> byte |
|----|----|----|----|----|----|----|----|----------------------|
| F7 | F6 | F5 | F4 | F3 | F2 | F1 | F0 | 2 <sup>nd</sup> byte |

The FADR command uses 2 bytes. This command is used to specify phrase to be played. The phrase to be played back are set by this command.

Playback will be started by START command after the phrase is specified.

For the phrase to be played back, set the phrase address of voice data in the ROM using the F9 to F0 bits.

The setting values of the FADR command are initialized at the power-down.




## 8. START command

| -                           |   |   |   |   |   |   |   |   |
|-----------------------------|---|---|---|---|---|---|---|---|
| <ul> <li>command</li> </ul> | 0 | 1 | 0 | 1 | 0 | 0 | 0 | 0 |

The START command is used to start playback a phrase. It is necessary to specify playback phrase using the FADR command before inputting this command.

The following figure shows the timing when starting playback.





## 9. MUON command

| <ul> <li>command</li> </ul> | 0  | 1  | 1  | 1  | 0  | 0  | 0  | 0  | 1 <sup>st</sup> byte |
|-----------------------------|----|----|----|----|----|----|----|----|----------------------|
|                             | M7 | M6 | M5 | M4 | М3 | M2 | M1 | M0 | 2 <sup>nd</sup> byte |

The MUON command uses 2 bytes. This command is used to insert the silence between two playback phrases. This command can be input when the NCR signal is "H" level. Set the silent time value after inputting this command.


The silent time length to be specified by M7 to M0 bits is able to be set by 256 steps at 4 ms interval between 20 ms and 1,024 ms.

The silent time length  $(t_{\text{mu}})$  is calculated by equation as below.

The silent time length should be set to 04h or higher (:t<sub>mu</sub> is 20ms or more).

$$T_{mu} = (2^{7} \times (M7) + 2^{6} \times (M6) + 2^{5} \times (M5) + 2^{4} \times (M4) + 2^{3} \times (M3) + 2^{2} \times (M2) + 2^{1} \times (M1) + 2^{0} \times (M0) + 1) \times 4ms$$

The following figure shows the timing of inserting the silence of 20 ms between the repetitions of phrase (F7 to F0 is 01h).



When the playback starts after the PLAY command is input and the address control of phrase-1 is over, the CBUSYB and NCR signals go to "H" level. Input the MUON command after this CBUSYB signal changes to "H" level. After the MUON command input, the NCR signal remains at "L" level until the end of phrase-1 playback. This status is the waiting for the phrase-1 playback to be finished.

When the phrase-1 playback is finished, the silence playback starts and the NCR signal goes to "H" level. Then, input the PLAY command again to playback phrase-1. Then, the NCR signal goes to "L" level again and the device enters a state of the waiting for the end of silence playback.

When the silence playback is finished and then the phrase-1 playback starts, the NCR signal goes to "H" level, and the device enters a status where it is possible to input the next PLAY or MUON command.

The BUSYB signal remains "L" level until the end of a series of playback.



## 10. SLOOP command

| <ul> <li>command</li> </ul> | 1 | 0 | 0 | 0 | 0 | 0 | 0 | 0 |
|-----------------------------|---|---|---|---|---|---|---|---|

The SLOOP command is used to set the repeat playback mode.


Use the CLOOP command to release repeat playback mode.

Since the SLOOP command is only valid during playback, be sure to input the SLOOP command while the NCR signal is "H" level after the PLAY command is input. The NCR signal is "L" level during repeat playback mode.

Once repeat playback mode is set, the current phrase is repeatedly played until the repeat playback setting is released by the CLOOP command or until playback is stopped by the STOP command. In the case of a phrase that was edited by the edit function, the edited phrase is repeatedly played.

The repeat playback mode is released if playback is stopped by the STOP command, therefore input the SLOOP command again if need to repeat playback again.

The following figure shows the SLOOP command input timing.



## Effective Range of SLOOP Command Input

After the PLAY command is input, input the SLOOP command within the command input enable time (:  $t_{cm}$ ) after NCR goes to "H". Then, the SLOOP command is available to repeat playback.



## 11. CLOOP command

| <ul> <li>command</li> </ul> | 1 | 0 | 0 | 1 | 0 | 0 | 0 | 0 |
|-----------------------------|---|---|---|---|---|---|---|---|

The CLOOP command is used to release the repeat playback mode.

When the repeat playback mode is released, the NCR signal goes to "H" level.

It is possible to input this command regardless of the NCR signal status during playback, but a prescribed command interval time  $(:t_{INT})$  is needed.



## 12. CVOL command

1<sup>st</sup> byte · command 1 0 1 0 0 0 0 0 0 CV4 CV3 CV0 2<sup>nd</sup> byte 0 0 CV2 CV1

The CVOL command uses 2 bytes. This command is used to adjust the playback volume. It is possible to input this command regardless of the NCR status. This command is not available during power down, transition to the power-up state or transition to the power-down state.

This command can adjust volume by 32-levels as shown in the table below. The initial value is set to 0 dB after the reset is released. Also, the setting of this command is initialized after the reset is released or during power-up.

| CV4-0 | Volume          | CV4-0 | Volume |
|-------|-----------------|-------|--------|
| 00    | 0dB             | 10    | -6.31  |
|       | (initial value) |       | -0.51  |
| 01    | -0.28           | 11    | -6.90  |
| 02    | -0.58           | 12    | -7.55  |
| 03    | -0.88           | 13    | -8.24  |
| 04    | -1.20           | 14    | -9.00  |
| 05    | -1.53           | 15    | -9.83  |
| 06    | -1.87           | 16    | -10.74 |
| 07    | -2.22           | 17    | -11.77 |
| 08    | -2.59           | 18    | -12.93 |
| 09    | -2.98           | 19    | -14.26 |
| 0A    | -3.38           | 1A    | -15.85 |
| 0B    | -3.81           | 1B    | -17.79 |
| 0C    | -4.25           | 1C    | -20.28 |
| 0D    | -4.72           | 1D    | -23.81 |
| 0E    | -5.22           | 1E    | -29.83 |
| 0F    | -5.74           | 1F    | OFF    |




## 13. AVOL command

| <ul> <li>command</li> </ul> | 0 | 0 | 0   | 0   | 1   | 0   | 0   | 0   | 1 <sup>st</sup> byte |
|-----------------------------|---|---|-----|-----|-----|-----|-----|-----|----------------------|
|                             | 0 | 0 | AV5 | AV4 | AV3 | AV2 | AV1 | AV0 | 2 <sup>nd</sup> byte |

The AVOL command uses 2 bytes. This command is used to adjust the playback volume. It is possible to input this command regardless of the NCR status. This command is not available during power down state, transition to power-up state or transition to power-down state.

This command can adjust volume by 50-levels as shown in the table below. The initial value is set to -4.0 dB after the reset is released. When the STOP command is input, the value set by the AVOL command is retained. When powered down, the value set by the AVOL command is initialized.

| AV5-0 | Volume (dB) | AV5-0 | Volume (dB)             | AV5-0 | Volume (dB) | AV5-0 | Volume (dB) |
|-------|-------------|-------|-------------------------|-------|-------------|-------|-------------|
| 3F    | +12.0       | 2F    | +4.0                    | 1F    | -8.0        | 0F    | -34.0       |
| 3E    | +11.5       | 2E    | +3.5                    | 1E    | -9.0        | 0E    | OFF         |
| 3D    | +11.0       | 2D    | +3.0                    | 1D    | -10.0       | 0D    | OFF         |
| 3C    | +10.5       | 2C    | +2.5                    | 1C    | -11.0       | 0C    | OFF         |
| 3B    | +10.0       | 2B    | +2.0                    | 1B    | -12.0       | 0B    | OFF         |
| 3A    | +9.5        | 2A    | +1.5                    | 1A    | -13.0       | 0A    | OFF         |
| 39    | +9.0        | 29    | +1.0                    | 19    | -14.0       | 09    | OFF         |
| 38    | +8.5        | 28    | +0.5                    | 18    | -16.0       | 08    | OFF         |
| 37    | +8.0        | 27    | +0.0                    | 17    | -18.0       | 07    | OFF         |
| 36    | +7.5        | 26    | -1.0                    | 16    | -20.0       | 06    | OFF         |
| 35    | +7.0        | 25    | -2.0                    | 15    | -22.0       | 05    | OFF         |
| 34    | +6.5        | 24    | -3.0                    | 14    | -24.0       | 04    | OFF         |
| 33    | +6.0        | 23    | -4.0<br>(initial value) | 13    | -26.0       | 03    | OFF         |
| 32    | +5.5        | 22    | -5.0                    | 12    | -28.0       | 02    | OFF         |
| 31    | +5.0        | 21    | -6.0                    | 11    | -30.0       | 01    | OFF         |
| 30    | +4.5        | 20    | -7.0                    | 10    | -32.0       | 00    | OFF         |





## 14. VPITCH command

· command

| 1   | 1   | 1   | 0   | 0   | 0   | 0   | 0   | 1 <sup>st</sup> byte |
|-----|-----|-----|-----|-----|-----|-----|-----|----------------------|
| PI7 | PI6 | PI5 | PI4 | PI3 | PI2 | PI1 | PI0 | 2 <sup>nd</sup> byte |

The VPITCH command is a 2-byte instruction command. This command reproduces the speech data with the pitch that is specified in the  $2^{nd}$  byte without changing the speed. This command converts the pitch for the original sound. The pitch conversion function (PI7-PI0) can convert the pitch of the original sounds up to  $\pm 20\%$  (40 levels) in 1% steps. See below for the pitch conversion data.

After reset release or at power-down, the command setting values are initialized.

| PI7 | PI6 | PI5 | PI4 | PI3 | PI2 | PI1 | PI0 | Change in pitch   |
|-----|-----|-----|-----|-----|-----|-----|-----|-------------------|
| 0   | 1   | 1   | 1   | 1   | 1   | 1   | 1   | 0.2               |
| 0   | 1   | 1   | 1   | 1   | 1   | 1   | 0   | 0.2               |
|     |     |     |     |     |     |     |     | :                 |
| 0   | 0   | 0   | 1   | 0   | 0   | 0   | 1   | 0.2               |
| 0   | 0   | 0   | 1   | 0   | 0   | 0   | 0   | 0.2               |
| 0   | 0   | 0   | 0   | 1   | 1   | 1   | 1   | 0.1875            |
| 0   | 0   | 0   | 0   | 1   | 1   | 1   | 0   | 0.175             |
| 0   | 0   | 0   | 0   | 1   | 1   | 0   | 1   | 0.1625            |
| 0   | 0   | 0   | 0   | 1   | 1   | 0   | 0   | 0.15              |
|     |     |     |     | :   |     |     |     | :                 |
| 0   | 0   | 0   | 0   | 0   | 1   | 0   | 0   | 0.05              |
| 0   | 0   | 0   | 0   | 0   | 0   | 1   | 1   | 0.0375            |
| 0   | 0   | 0   | 0   | 0   | 0   | 1   | 0   | 0.025             |
| 0   | 0   | 0   | 0   | 0   | 0   | 0   | 1   | 0.0125            |
| 0   | 0   | 0   | 0   | 0   | 0   | 0   | 0   | 0 (initial value) |
| 1   | 1   | 1   | 1   | 1   | 1   | 1   | 1   | -0.0125           |
| 1   | 1   | 1   | 1   | 1   | 1   | 1   | 0   | -0.025            |
| 1   | 1   | 1   | 1   | 1   | 1   | 0   | 1   | -0.0375           |
| 1   | 1   | 1   | 1   | 1   | 1   | 0   | 0   | -0.05             |
|     |     |     |     |     |     |     |     | :                 |
| 1   | 1   | 1   | 1   | 0   | 1   | 0   | 0   | -0.15             |
| 1   | 1   | 1   | 1   | 0   | 0   | 1   | 1   | -0.1625           |
| 1   | 1   | 1   | 1   | 0   | 0   | 1   | 0   | -0.175            |
| 1   | 1   | 1   | 1   | 0   | 0   | 0   | 1   | -0.1875           |
| 1   | 1   | 1   | 1   | 0   | 0   | 0   | 0   | -0.2              |
| 1   | 1   | 1   | 0   | 1   | 1   | 1   | 1   | -0.2              |
|     |     |     |     |     |     |     |     | :                 |
| 1   | 0   | 0   | 0   | 0   | 0   | 0   | 1   | -0.2              |
| 1   | 0   | 0   | 0   | 0   | 0   | 0   | 0   | -0.2              |



## 15. VSPD command

· command

| 1   | 1   | 0   | 1   | 0   | 0   | 0   | 0   | 1 <sup>st</sup> byte |
|-----|-----|-----|-----|-----|-----|-----|-----|----------------------|
| SD7 | SD6 | SD5 | SD4 | SD3 | SD2 | SD1 | SD0 | 2 <sup>nd</sup> byte |

The VSPD command is a 2-byte instruction command. This command reproduces the speech data with the speed that is specified in the  $2^{nd}$  byte without changing the pitch. For the playback speed (SD7-SD0), 150 steps can be set from 0.5 times to 2.0 times at time-step increments of 0.01.

See below for the playback speed.

After reset release or at power-down, the command setting values are initialized.

| SD7 | SD6 | SD5 | SD4 | SD3 | SD2 | SD1 | SD0 | Playback speed<br>(magnification) |
|-----|-----|-----|-----|-----|-----|-----|-----|-----------------------------------|
| 0   | 1   | 1   | 1   | 1   | 1   | 1   | 1   | 2.00                              |
| 0   | 1   | 1   | 1   | 1   | 1   | 1   | 0   | 2.00                              |
|     |     | :   |     |     |     |     |     |                                   |
| 0   | 1   | 1   | 0   | 0   | 1   | 0   | 1   | 2.00                              |
| 0   | 1   | 1   | 0   | 0   | 1   | 0   | 0   | 2.00                              |
| 0   | 1   | 1   | 0   | 0   | 0   | 1   | 1   | 1.99                              |
| 0   | 1   | 1   | 0   | 0   | 0   | 1   | 0   | 1.98                              |
| 0   | 1   | 1   | 0   | 0   | 0   | 0   | 1   | 1.97                              |
|     |     |     |     | :   |     |     |     | •                                 |
| 0   | 0   | 0   | 0   | 0   | 0   | 1   | 1   | 1.03                              |
| 0   | 0   | 0   | 0   | 0   | 0   | 1   | 0   | 1.02                              |
| 0   | 0   | 0   | 0   | 0   | 0   | 0   | 1   | 1.01                              |
| 0   | 0   | 0   | 0   | 0   | 0   | 0   | 0   | 1.00 (initial value)              |
| 1   | 1   | 1   | 1   | 1   | 1   | 1   | 1   | 0.99                              |
| 1   | 1   | 1   | 1   | 1   | 1   | 1   | 0   | 0.98                              |
| 1   | 1   | 1   | 1   | 1   | 1   | 0   | 1   | 0.97                              |
|     |     |     |     | :   |     |     |     | •                                 |
| 1   | 1   | 0   | 1   | 0   | 0   | 0   | 1   | 0.53                              |
| 1   | 1   | 0   | 1   | 0   | 0   | 0   | 0   | 0.52                              |
| 1   | 1   | 0   | 0   | 1   | 1   | 1   | 1   | 0.51                              |
| 1   | 1   | 0   | 0   | 1   | 1   | 1   | 0   | 0.50                              |
| 1   | 1   | 0   | 0   | 1   | 1   | 0   | 1   | 0.50                              |
|     |     | •   |     |     |     |     |     |                                   |
| 1   | 0   | 0   | 0   | 0   | 0   | 0   | 1   | 0.50                              |
| 1   | 0   | 0   | 0   | 0   | 0   | 0   | 0   | 0.50                              |



# RECOMMENDATION FOR SPEECH SPEED CONVERSION AND PITCH CONVERSION FUNCTION

If user want to use speed and pitch conversion function with keeping speech quality, it's better to use that function on below conditions.

- sampling frequency : 12.8 / 16.0 / 21.3 / 24.0 / 32.0 kHz

- speed conversion : 0.80 to 2.00 times- pitch conversion : -10 to +10 %

Then these functions work for speech data only. Not work for melody or natural sound.



## TERMINATION OF THE SG PIN

The SG pin is the signal ground for the built-in speaker amplifier. Connect a capacitor between this pin and the analog ground (: DGND) pin to prevent the trouble caused by noises.

Recommended capacitance value is shown below. However, it is important to evaluate and decide using the own board.

Also, start playback after each output voltage is stabilized.

| Pin | Recommended capacitance value | Remarks   |
|-----|-------------------------------|---|
| SG  | 0.1 μF ±20%                   | The time to stabilize voltage of the speaker outputs (:SPM and SPP) is longer, if use the larger capacitance. |

# TERMINATION OF THE $V_{DDL}$ AND $V_{DDR}$ PINS

The  $V_{DDL}$  pin is the regulator output that is power supply for the internal logic circuitry. Connect a capacitor between this pin and the ground (: DGND) pin to prevent the trouble caused by noises and to hold power supply voltage steady.

The recommended capacitance value is shown below. However, it is important to evaluate and decide using the own board.

Also, start the next operation after each output voltage is stabilized.

|                 | Pin                   | Recommended capacitance value | Remarks  |
|-----------------|-----------------------|-------------------------------|--|
| V <sub>DI</sub> | $_{ m DL},V_{ m DDR}$ | 10 μF ±20%                    | The time to stabilize voltage of each output is longer, if use the larger capacitance. |




## POWER SUPPLY WIRING

The power supplies of this LSI are divided into the following two:

- Power supply for logic circuitry (: DV<sub>DD</sub>)
- Power supply for speaker amplifier (: SPV<sub>DD</sub>)

As shown in the figure below, supply  $DV_{DD}$  and  $SPV_{DD}$  from the same power supply, and separate them into analog and logic power supplies in the wiring.





# RECOMMENDED CERAMIC RESONATOR


Recommended ceramic resonators for oscillation and conditions are shown below for reference.

**KYOCERA** Corporation

|           |                   | Optimal load capacity |            |             |             |                             |                                     |  |
|-----------|-------------------|-----------------------|------------|-------------|-------------|-----------------------------|-------------------------------------|--|
| Freq [Hz] | Туре              | C1<br>[pF]            | C2<br>[pF] | Rf<br>[Ohm] | Rd<br>[Ohm] | Supply voltage<br>Range [V] | Operating Temperature<br>Range [°C] |  |
| 4.096M    | PBRC4.096MR50X000 | 15(built-in)          |            |             |             | 2.7 to3.3<br>4.5 to5.5      | -40 to +85                          |  |

Note: C1 and C2 are capacitors built-in resonator.


# Circuit diagram



**TDK Corporation** 

|           | 11 Col Politicol |               |      |       |      |                |                       |  |  |
|-----------|------------------|---------------|------|-------|------|----------------|-----------------------|--|--|
|           |                  | Conditions    |      |       |      |                |                       |  |  |
| Freq [Hz] | Туре             | C1            | C2   | Rf    | C1   | Supply voltage | Operating Temperature |  |  |
|           |                  | [pF]          | [pF] | [Ohm] | [pF] | Range [V]      | Range [°C]            |  |  |
| 4.000M    | FCR4.0MXC5       | 30 (built-in) |      |       |      | 2.7 to3.6      | -40 to +85            |  |  |
| 4.000IVI  | FCR4.0MXC5       |               |      |       |      | 4.5 to5.5      | -40 10 103            |  |  |
| 4.096M    | FCR4.09MXC5      | 30 (built-in) |      |       |      | 2.7 to3.6      | -40 to +85            |  |  |
| 4.096101  | FCR4.09MXC5      |               |      |       |      | 4.5 to5.5      |                       |  |  |

# Circuit diagram






# **MURATA Corporation**

|           | Туре   |                  | Optimal load capacity |               |             |             |                                |  |  |  |
|-----------|--------|------------------|-----------------------|---------------|-------------|-------------|--------------------------------|--|--|--|
| Freq [Hz] |        |                  | C1<br>[pF]            | C2<br>[pF]    | Rf<br>[Ohm] | Rd<br>[Ohm] | Supply<br>voltage<br>Range [V] | Operating<br>Temperature<br>Range [°C] |  |  |
|           | SMD    | CSTCR4M00G55-R0  | 39 (Built-in)         |               |             |             | 2.7 to 3.6                     |  |  |  |
| 4.000M    | Leaded | CSTLS4M00G56-B0  | 47 (Built-in)         |               |             | 0           | 2.7 10 3.0                     |  |  |  |
| 4.000101  | SMD    | CSTCR4M00G55-R0  | 39 (Built-in)         |               |             |             | 4.5 to 5.5                     |  |  |  |
|           | Leaded | CSTLS4M00G56-B0  | 47 (B                 | 47 (Built-in) |             |             | 4.5 10 5.5                     | -40 to +85*                            |  |  |
|           | SMD    | CSTCR4M09G55-R0  | 39 (B                 | 39 (Built-in) |             |             | 2.7 to 3.6                     | -40 10 +65                             |  |  |
| 4.096M    | Leaded | CSTLS4M09G56-B0  | 47 (Built-in)         |               |             | 0           | 2.7 10 3.0                     |  |  |  |
| 4.090101  | SMD    | CSTCR4M09G55-R0  | 39 (Built-in)         |               |             |             | 4.5 to 5.5                     |  |  |  |
|           | Leaded | CSTLS 4M09G56-B0 | 47 (B                 | 47 (Built-in) |             |             | 4.5 (0 5.5                     |  |  |  |

Note: C1 and C2 are capacitors built-in resonator.


# Circuit diagram






# **APPLICATION CIRCUIT**

ML2272X:  $DV_{DD}=SPV_{DD}=5V$ 




# ML2272X: $DV_{DD}=SPV_{DD}=3V$






# ML2276X: $DV_{DD}$ = $SPV_{DD}$ =5V




# ML2276X: $DV_{DD}$ = $SPV_{DD}$ =3V





## PACKAGE DIMENSIONS



Notes for Mounting the Surface Mount Type Package:

The surface mount type packages are very susceptible to heat in reflow mounting and humidity absorbed in storage. Therefore, before you perform reflow mounting, contact ROHM's responsible sales person for the product name, package name, pin number, package code and desired mounting conditions (reflow method, temperature and times).



# **REVISION HISTORY**

|                  |               | Pa                  | ge                 |  |
|------------------|---------------|---------------------|--------------------|--|
| Document No.     | Date          | Previous<br>Edition | Current<br>Edition | Description  |
| PEDL2272XFULL-01 | Dec. 17, 2007 | _                   | _                  | Preliminary edition 1  |
| FEDL2272XFULL-01 | Apr. 18, 2008 | _                   | _                  | Final edition 1  |
| FEDL2272XFULL-02 | May. 29, 2008 | _                   | _                  | Final edition 2  |
|                  |               | 5,6                 | 5,6                | Common terminal explanation attribute change (TESTI1,SPP,SPM)    |
|                  | Mar. 25, 2009 | 11                  | 11                 | Max value change within the range of LINE output voltage         |
| FEDL2272XFULL-03 |               | 12                  | 12                 | Min, Typ, and Max value change of CBUSYB ("L" level output time) |
| FEDLZZ/ZAFOLL-03 |               | 25,34,35,<br>36,37  | 24,33,34,<br>35,36 | Bit name of AMODE command (PUP->POP)                             |
|                  |               | 53,54               | 53,54              | Modify application circuit                                       |
|                  |               | 45                  | 45                 | Correct value for AVOL   |
| FEDL2272XFULL-04 | Aug. 25, 2011 | 44                  | 44                 | Modify AVOL table.   |
| FEDL2272XFULL-05 | Aug. 30, 2011 | 24-47               | 24-47              | Delete the explanation about "channel".                          |
| FEDL227XX-06     | Oct. 16, 2013 | 13                  | 13                 | Modify tDOD1.<br>( SCK rise edge -> SCK fall edge )              |



## **NOTES**

No copying or reproduction of this document, in part or in whole, is permitted without the consent of LAPIS Semiconductor Co., Ltd.

The content specified herein is subject to change for improvement without notice.

The content specified herein is for the purpose of introducing LAPIS Semiconductor's products (hereinafter "Products"). If you wish to use any such Product, please be sure to refer to the specifications, which can be obtained from LAPIS Semiconductor upon request.

Examples of application circuits, circuit constants and any other information contained herein illustrate the standard usage and operations of the Products. The peripheral conditions must be taken into account when designing circuits for mass production.

Great care was taken in ensuring the accuracy of the information specified in this document. However, should you incur any damage arising from any inaccuracy or misprint of such information, LAPIS Semiconductor shall bear no responsibility for such damage.

The technical information specified herein is intended only to show the typical functions of and examples of application circuits for the Products. LAPIS Semiconductor does not grant you, explicitly or implicitly, any license to use or exercise intellectual property or other rights held by LAPIS Semiconductor and other parties. LAPIS Semiconductor shall bear no responsibility whatsoever for any dispute arising from the use of such technical information.

The Products specified in this document are intended to be used with general-use electronic equipment or devices (such as audio visual equipment, office-automation equipment, communication devices, electronic appliances and amusement devices).

The Products specified in this document are not designed to be radiation tolerant.

While LAPIS Semiconductor always makes efforts to enhance the quality and reliability of its Products, a Product may fail or malfunction for a variety of reasons.

Please be sure to implement in your equipment using the Products safety measures to guard against the possibility of physical injury, fire or any other damage caused in the event of the failure of any Product, such as derating, redundancy, fire control and fail-safe designs. LAPIS Semiconductor shall bear no responsibility whatsoever for your use of any Product outside of the prescribed scope or not in accordance with the instruction manual.

The Products are not designed or manufactured to be used with any equipment, device or system which requires an extremely high level of reliability the failure or malfunction of which may result in a direct threat to human life or create a risk of human injury (such as a medical instrument, transportation equipment, aerospace machinery, nuclear-reactor controller, fuel-controller or other safety device). LAPIS Semiconductor shall bear no responsibility in any way for use of any of the Products for the above special purposes. If a Product is intended to be used for any such special purpose, please contact a ROHM sales representative before purchasing.

If you intend to export or ship overseas any Product or technology specified herein that may be controlled under the Foreign Exchange and the Foreign Trade Law, you will be required to obtain a license or permit under the Law.

Copyright 2007 - 2013 LAPIS Semiconductor Co., Ltd.